



3M™ Polycarbonate Crowns

Coverage

Short- or long-term

Dentition

Permanent

Selection

Anterior and bicuspid

Key Traits

- Polycarbonate resin with microglass fibers
- Strong and durable
- Contours and crimps similar to metal crowns
- Esthetic U62 shade

3M™ Polycarbonate Crowns – C180 Kit

Crown drawer only: C-000

Upper Right						CENTRALS								Upper Left					
100	101	10	11	12	13	14	15	16	17	18	19	102	103						

Upper Right						LATERALS								Upper Left					
2	20	21	22	23	24									25	26	27	28	29	200

Upper and Lower Right						CUSPIDS								Upper and Lower Left					
300	301	30	31	32	33	34	35	36	37	38	39	302	303						

FIRST BICUSPIDS					SECOND BICUSPIDS				
40	41	42	43	44	54	53	52	51	50

LOWER INCISORS (LONG)					LOWER INCISORS (SHORT)				
60	61	62	63	64	69	68	67	66	65

3M™ Polycarbonate Crown Conversion Chart

MESIAL DISTAL WIDTH IN MM	3M™ Polycarbonate		Bosworth™		Caulk™	
	LEFT	RIGHT	LEFT	RIGHT	LEFT	RIGHT
UPPER CENTRALS						
6.5						
7.0						
7.5			LM6	RM6	E3	E4
7.7	15	14	LM5	RM5		
8.0	16	13	LM4	RM4	D3	D4
8.2	17	12				
8.3			LM3	RM3		
8.4	18	11				
8.5						
8.8			LM2	RM2	C3	C4
8.9	19	10				
9.0						
9.2						
9.4	102	101	LM1	RM1	B3	B4
9.6						
10.0					A3	A4
10.1	103	100				
UPPER LATERALS						
4.5						
5.0						
5.5						
5.6			LL4	RL4	E2	E2
5.8	25	24				
6.0						
6.3			LL3	RL3	D2	D2
6.4	26	23				
6.5	27	22				
6.8					C2	C2
7.0	28	21	LL2	RL2	B2	B2
7.1	29	20				
7.2						
7.3			LL1	RL1	A2	A2
7.6	200	2				
CUSPIDS (continued on page 4)						
6.5						
6.6						
7.0						
7.2			LC4	RC4	E1	E6
7.4						
7.5	35	34	LC3	RC3	D1	D6

3M™ Polycarbonate Crown Conversion Chart (continued)

MESIAL DISTAL WIDTH IN MM	3M™ Polycarbonate		Bosworth™		Caulk™	
	LEFT	RIGHT	LEFT	RIGHT	LEFT	RIGHT
C U S P I D S (continued from page 3)						
7.6						
7.7	36	33				
7.8	37	32	LC2	RC2	C1	C6
8.0						
8.1	38	31				
8.3	39	30				
8.4						
8.5			LC1	RC1	B1	B6
8.6	302	301				
8.8						
8.9					A1	A6
9.0	303	300				
B I C U S P I D S						
6.0						
6.2	44		B4		F-7	F-8
6.4	54					
6.5	43					
6.8	42 / 53					
6.9	41 / 52		B3		F-5	F-6
7.2	40 / 51		B2		F-3	F-4
7.5	50				F-1	F-2
7.6						
L O W E R I N C I S O R S						
4.8						
4.9	65					
5.0			13-L / 16-S		H-5	H-5
5.1	66		12-L / 15-S			
5.2	64					
5.3	67		11-L / 15-S		H-4	H-4
5.4	63					
5.6	62		10-L / 14-S		H-3	H-3
5.7	68					
5.8	61 / 69					
6.0					H-2	H-2
6.3	60				H-1	H-1
6.4						